



Hexagon socket head cap screw with low head and pilot recess DIN 6912 Steel Plain 08.8 M20X45

Article number	07030.200.045
Brand	-
UBB	955351061994
UNSPSC	31161605
EAN	8715492053916
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	45 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

DIN	6912
-----	------

or with the steel
grade only, e.g. 'A2'.

FABORY

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
dh	10
dk	30
Full thread if L ≤	60
k	12
L (mm)	45
P	2.5
s	17

Technical Drawing

