



Assembly set for pressure vessels ISO 4014/4032 Ocel Žárový zinek 5.6/5.2 M16X65

Objednací číslo	08753.160.065
Značka	-
UBB	500650921298
UNSPSC	31161620
EAN	8717077306592
BAL. od 25	Pouze celé balení

Technické parametry

Průměr	M16
Délka	65 mm
Třída	5.6/5.2
Typ drážky	Šestihran
Tvar hlavy	Šestihranná hlava
Materiál	Ocel
Směr závitů	Pravý
Povrchová úprava	Žárový zinek
Závit	Metrický závit

Standardy

ISO	4014/4032
-----	-----------

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204

3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy.

Technická specifikace

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L > 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	65
m (max.)	14.8
P	2
s	24

Technický nákres

