



KIPP Indexing plungers, high, lockout type, without locknut Metrický jemný závit Nerezová ocel 1.4305, tvrzený čep, plastová rukojeť 8MM

Objednací číslo	58581.000.008
Značka	-
UBB	500689867728
UNSPSC	31162807
EAN	4059245013364
BAL. od 2	Pouze celé balení

Technické parametry

D1_MM	16mm
Materiál	Nerezocel
Technický materiál	1.4305
Závit	Metrický jemný závit
Info	Material: Stainless steel. Threaded sleeve 1.4305 Indexing pin 1.4034 Mushroom knob black grey thermoplastic. Version: Indexing pin hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. The lockout types are recommended for applications in

Standardy

which the pin is disengaged over extended periods and should be prevented from springing back..

Technická specifikace

D	8
D1	16
D2	33
F1 = springiness beginning in N	15
F2 = springiness end in N	35
F x 30°	2.3
H	8
L1	26
L2	10
L3	23
L	74
P	1.5
SW1	19

Technický náčrt

