



KIPP Indexing plungers with threaded pin, with locknut Metrický jemný závit Nerezová ocel 1.4305, netvrzený kolík 8MM

Objednací číslo 58593.000.008

Značka -

UBB 500689874815

UNSPSC 31162807

EAN 4059245014194

BAL. od 2 Pouze celé balení

Technické parametry

D1_MM 16mm

Materiál Nerezocel

Technický materiál 1.4305

Závit Metrický jemný závit

Info Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305. Version: Indexing pin not hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been disengaged. Special grips can be fitted on the projecting threaded pin. This pin is also suitable for automatic actuation e.g. program controlled

Standardy

pneumatic cylinder
or by remote control
using Bowden
cables.

Technická specifikace

D	8
D1	16
D2	8
F1 = springiness beginning in N	15
F2 = springiness end in N	35
F x 30°	2.3
H	8
L1	26
L2	10
L3	12
L4	23
L	56
P	1.5
SW1	19
SW2	24

Technický náčrt

