



KIPP Indexing plungers with threaded pin, with locknut Metrický jemný závit Nerezová ocel 1.4305, netvrzený kolík 10MM

Objednací číslo	58593.000.010
Značka	-
UBB	500689874997
UNSPSC	31162807
EAN	4059245014200
BAL. od 1	Pouze celé balení

Technické parametry

D1_MM	20mm
Materiál	Nerezocel
Technický materiál	1.4305
Závit	Metrický jemný závit
Info	Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305. Version: Indexing pin not hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been disengaged. Special grips can be fitted on the projecting threaded pin. This pin is also suitable for automatic actuation e.g. program controlled

Standardy

pneumatic cylinder
or by remote control
using Bowden
cables.

Technická specifikace

D	10
D1	20
D2	8
F1 = springiness beginning in N	15
F2 = springiness end in N	34
F x 30°	2.8
H	10
L1	28
L2	12
L3	12
L4	25
L	62
P	1.5
SW1	22
SW2	30

Technický náčrt

