



KIPP Indexing plungers without collar, with locknut Metrický jemný závit Nerezová ocel 1.4305, netvrzený kolík 6MM

Objednací číslo 58605.000.006

Značka -

UBB 500689882578

UNSPSC 31162807

EAN 4059245015184

BAL. od 4 Pouze celé balení

Technické parametry

D1_MM 12mm

Materiál Nerezocel

Technický materiál 1.4305

Závit Metrický jemný závit

Info Material: Stainless steel threaded sleeve 1.4305 Indexing pin 1.4305 Mushroom knob black grey thermoplastic. Version: Indexing pin not hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. A screw-in washer can be supplied to help screw in the indexing plungers.

Standardy

The washer is slid beneath the disengaged mushroom knob so that the carrier pins engage in the slot.

Technická specifikace

D	6
D1	12
D2	25
F1 = springiness beginning in N	6
F2 = springiness end in N	14
F x 30°	1.8
H	6
L1	28
L2	17.7
L	51.7
P	1.5
SW	19

Technický náčrt

