



M10X40

Objednací číslo	93361FIS
Značka	-
UBB	500616868419
UNSPSC	31162905
EAN	4006209933619
BAL. od 1	Pouze celé balení

Technické parametry

Info	T-head bolt for all standard rail profiles with 15 mm and 17 mm slot width. Advantages / Benefits: Simple, fast and effective installation. Fewer individual parts than with traditional fixings. Simple alignment in the rail. As connection element between: Rail load-bearing constructions and pipe clamps. Cantilever brackets and pipe clamps.
------	--

Standardy

Technická specifikace

Technický náčrtek

