

Vysokozátěžová kotva typ FH-B M16X160/60



Objednací číslo	97038FIS
Značka	-
UBB	500616707534
UNSPSC	31162101
EAN	4006209970386
BAL. od 10	Pouze celé balení

Technické parametry

Průměr	M16
--------	-----

Info

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should comply with the

Standardy

FABORY complete European
Technical Approval
(ETA), this approval
is also available on
request.

Technická specifikace

Technický náčrtek

