

Hexagon head screw ISO 4017 Steel Zinc plated with thick Cr(III) passivation 8.8 M12X80

Article number	01237.120.080
Brand	-
UBB	500648288610
UNSPSC	31161620
EAN	8717077234529
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

NF	E25-114
DIN	933
NEN	1568
ISO	4017
ASME	B18.2.3.1M

Technical Specification

d-D	M12
k	7.5
L (mm)	80
P	1.75
s	18

Technical Drawing

