



innensechskantschrauben mit niedrigem Zylinderkopf DIN 7984 DIN 7984 Stahl Blank 010.9 M4X12

Artikelnummer	07105.040.012
Marke	-
UBB	953351827886
UNSPSC	31161605
EAN	8715492063908
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	M4
Länge	12 mm
Klasse	010.9
Antriebsart	Innensechskant
Kopfform	Zylinderkopf, niedrige form
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Blank
Gewinde	Metrisches Gewinde

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement. Due
to the unfavourable
head geometry
these fasteners
have reduced
loadability. Steel
fasteners with
reduced loadability
are marked with a
'0' preceding the
property class mark,
e.g. '010.9'. Stainless
steel fasteners with

Standards

DIN	7984
-----	------

reduced loadability
are either marked
with a '0' preceding
the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technische Spezifikation

b (min.)	14
d-D	M4
dk	7
Full thread if $L \leq$	20
k	2.8
L (mm)	12
P	0.7
s	2.5

Technische Zeichnung

