



Senkkopfschrauben ISO 10642 Stahl Blank 010.9 M8X120

Artikelnummer	07400.080.120
Marke	-
UBB	500645108324
UNSPSC	31161518
EAN	8717077060715
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	M8
Länge	120 mm
Klasse	010.9
Antriebsart	Innensechskant
Kopfform	Senkkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Blank
Gewinde	Metrisches Gewinde

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.All
thread lengths
are guide values
only and may
deviate.Due to
the unfavourable
head geometry
these fasteners
have reduced
loadability.Steel
fasteners with
reduced loadability
are marked with a
'0' preceding the
property class mark,

Standards

DIN	≈7991
ISO	10642

e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technische Spezifikation

b (min.)	28
d-D	M8
dk (max.)	16.43
Full thread if $L \leq$	45
k (max.)	4.96
L (mm)	120
P	1.25
s	5
α	90

Technische Zeichnung

