



Senkkopfschrauben ISO 10642 Stahl Elektrolytisch verzinkt 8.8 M8X20

Artikelnummer	07470.080.020
Marke	-
UBB	950351489725
UNSPSC	31161518
EAN	8715492151544
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	M8
Länge	20 mm
Klasse	08.8
Antriebsart	Innensechskant
Kopfform	Senkkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Elektrolytisch verzinkt
Gewinde	Metrisches Gewinde

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

Standards

ISO	10642
DIN	≈7991

FABORY with a '0' preceding
the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technische Spezifikation

b (min.)	28
d-D	M8
dk (max.)	16.43
Full thread if $L \leq$	45
k (max.)	4.96
L (mm)	20
P	1.25
s	5
α	90

Technische Zeichnung

