



Senkkopfschrauben ISO 10642 Stahl Elektrolytisch verzinkt 8.8 M10X70

Artikelnummer	07470.100.070
Marke	-
UBB	950351491945
UNSPSC	31161518
EAN	8715492151766
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	M10
Länge	70 mm
Klasse	08.8
Antriebsart	Innensechskant
Kopfform	Senkkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Elektrolytisch verzinkt
Gewinde	Metrisches Gewinde

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

Standards

DIN	≈7991
ISO	10642

FABORY with a '0' preceding
the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technische Spezifikation

b (min.)	32
d-D	M10
dk (max.)	20.69
Full thread if $L \leq$	50
k (max.)	6.2
L (mm)	70
P	1.5
s	6
α	90

Technische Zeichnung

