



Assembly set for pressure vessels ISO 4014/4032 Stahl Feuerverzinkt 5.6/5.2 M16X80

Artikelnummer	08753.160.080
Marke	-
UBB	500650921520
UNSPSC	31161620
EAN	8717077306622
PKG. von 25	Nur komplette Verpackung

Technische Parameter

Durchmesser	M16
Länge	80 mm
Klasse	5.6/5.2
Antriebsart	Hexagon
Kopfform	Sechskantkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Feuerverzinkt
Gewinde	Metrisches Gewinde

Info	Specific features of fasteners for pressure vessels:Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from –10°C up to +300°C.Meets the requirements of AD2000-W7, TRD106 and DIN 267-13Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a
------	---

Standards

ISO	4014/4032
-----	-----------

FABORY

certificate EN 10204

3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.

This recognition is
equally accepted
by Lloyd's Register
Energy.

Technische Spezifikation

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L > 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	80
m (max.)	14.8
P	2
s	24

Technische Zeichnung

