



Assembly set for pressure vessels, fully threaded ISO 4017/4032 Steel (AD-W7) Feuerverzinkt 5.6/5.2 für Druckbehälter M16X35

Artikelnummer	08762.160.035
Marke	-
UBB	500648359163
UNSPSC	31161620
EAN	8717077245839
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	M16
Länge	35 mm
Klasse	5.6/5.2
Antriebsart	Hexagon
Kopfform	Sechskantkopf
Material	Steel (AD-W7)
Gewinderichtung	Rechts
Oberfläche	Feuerverzinkt
Gewinde	Metrisches Gewinde

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13 Manufacturers

Standards

ISO 4017/4032

included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy.für Druckbehälter

Technische Spezifikation

d-D	M16
k	10
L (mm)	35
m (max.)	14.8
P	2
s	24

Technische Zeichnung

