



**Heco-Fix Kreuzschlitz
Linsenkopf Stahl
Elektrolytisch verzinkt
3X16MM**

Artikelnummer	29345.030.016
Marke	-
UBB	500500463384
UNSPSC	31161508
EAN	4019787052504
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	3 mm
Länge	16 mm
Antriebsart	Pozidriv
Kopfform	Linsenkopf
Material	Stahl
Oberfläche	Elektrolytisch verzinkt

Standards

Info	All dimensions are guide values and may deviate dependent on the manufacturer. Specific features HECO-FIX PLUS screws for chipboard: Reduction of required drive torque of up to 30%. Easier handling. Substantially higher screwing performance on using storage battery screw drivers. Axial forces are reduced, thereby less wear of screw driver bits. By means of the tooth geometry, a higher
------	---

unscrewing moment is nevertheless, achieved and consequently, a secure screwed connection is obtained. Warning: electro-galvanizing of these products may cause hydrogen embrittlement.

Technische Spezifikation

D (mm)	3
dk (max.)	5.9
k (max.)	2.2
L (mm)	16
No. cross recess	1

Technische Zeichnung

