

MaxxFast Ankerbolzen
ThruFast Stahl Elektrolytisch
verzinkt 6X100



Artikelnummer	30550.060.100
Marke	-
UBB	500577350084
UNSPSC	31162101
EAN	8715494322706
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	6 mm
Länge	100 mm
Material	Stahl
Oberfläche	Elektrolytisch verzinkt
Gewinde	Metrisches Gewinde

Standards

Info	Nur volle Verpackungseinheiten.do = Nominal diameter of drill bits = Width across flatsring Ø = Washer diameterdf = Diameter of clearance hole in the fixtureh1 = Recommended drilling depthh(nom) = Minimum hole depthhef = Effective anchorage depthScr,N = Spacing characteristicCcr,N = Edge distance characteristicctfix(max) = Grip rangeTinst = Tightening torque in NmNrec = Recommended load in kNThe allowable
------	---

load is valid for
one single anchor,
at non-cracked
concrete (pressure
zone) with concrete
class C20/25, incl.
partial safety factor
 $\gamma_f = 1,4$ and if the
Scr, N and Ccr,
N are taken in to
account.

Technische Spezifikation

Ccr, N	60
d-D	M6
df	7
D (mm)	6
do	6
h (nom.)	49.5
h1	55
hef	40
L (mm)	100
Nrec	3.93
Ring ø	12
s	10
Scr, N	120
tfix(max.)	42
Tinst	7

Technische Zeichnung

