


Spiral-Spannstift, geschlitzt,
schwer ISO 8752 Federstahl
420-560 HV30 6X65MM



Artikelnummer	39100.060.065
Marke	-
UBB	950359356421
UNSPSC	31163201
EAN	8715492803962
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	6 mm
Länge	65 mm
Material	Federstahl
Material technisch	420-560 HV30

Standards

BS	7060
ISO	8752
NEN	2458
DIN	1481

Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer.V = minimum shear strength, double, in kN.The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of slotted spring-type straight pins:These
------	---

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	1.2
d1 (max.)	6.7
d1 (min.)	6.4
d2 ≈	4
D (mm)	6
L (mm)	65
s	1.2
V	26.04

Technische Zeichnung

