


Spiral-Spannstift, geschlitzt, schwer ISO 8752 Federstahl 420-560 HV30 12X30MM



Artikelnummer	39100.120.030
Marke	-
UBB	950359045230
UNSPSC	31163201
EAN	8715492805126
PKG. von 25	Nur komplette Verpackung

Technische Parameter

Durchmesser	12 mm
Länge	30 mm
Material	Federstahl
Material technisch	420-560 HV30

Standards

NEN	2458
BS	7060
ISO	8752
DIN	1481

Info	Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These
------	---

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	2
d1 (max.)	12.8
d1 (min.)	12.5
d2 ≈	7.5
D (mm)	12
L (mm)	30
s	2.5
V	104.1

Technische Zeichnung

