


Spiral-Spannstift, geschlitzt,
schwer ISO 8752 Federstahl
420-560 HV30 14X50MM



Artikelnummer	39100.140.050
Marke	-
UBB	950359046550
UNSPSC	31163201
EAN	8715492805584
PKG. von 25	Nur komplette Verpackung

Technische Parameter		Standards	
Durchmesser	14 mm	NEN	2458
Länge	50 mm	BS	7060
Material	Federstahl	DIN	1481
Material technisch	420-560 HV30	ISO	8752
Info	Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These		

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	2
d1 (max.)	14.8
d1 (min.)	14.4
d2 ≈	8.5
D (mm)	14
L (mm)	50
s	3
V	144.7

Technische Zeichnung

