


Spiral-Spannstift, geschlitzt,
schwer ISO 8752 Federstahl
420-560 HV30 14X90MM



Artikelnummer	39100.140.090
Marke	-
UBB	950359046899
UNSPSC	31163201
EAN	8715492805669
PKG. von 25	Nur komplette Verpackung

Technische Parameter		Standards	
Durchmesser	14 mm	DIN	1481
Länge	90 mm	BS	7060
Material	Federstahl	NEN	2458
Material technisch	420-560 HV30	ISO	8752
Info	Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These		

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	2
d1 (max.)	14.8
d1 (min.)	14.4
d2 ≈	8.5
D (mm)	14
L (mm)	90
s	3
V	144.7

Technische Zeichnung

