


Spiral-Spannstift, geschlitzt,
schwer ISO 8752 Federstahl
420-560 HV30 16X90MM



Artikelnummer	39100.160.090
Marke	-
UBB	950359369390
UNSPSC	31163201
EAN	8715492805928
PKG. von 5	Nur komplette Verpackung

Technische Parameter

Durchmesser	16 mm
Länge	90 mm
Material	Federstahl
Material technisch	420-560 HV30

Standards

BS	7060
DIN	1481
NEN	2458
ISO	8752

Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer.V = minimum shear strength, double, in kN.The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of slotted spring-type straight pins:These
------	---

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	2
d1 (max.)	16.8
d1 (min.)	16.5
d2 ≈	10.5
D (mm)	16
L (mm)	90
s	3
V	171

Technische Zeichnung

