


Spiral-Spannstift, geschlitzt, schwer ISO 8752 Federstahl 420-560 HV30 Elektrolytisch verzinkt 5X40MM



Artikelnummer	39110.050.040
Marke	-
UBB	950359527120
UNSPSC	31163201
EAN	8715492807076
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	5 mm
Länge	40 mm
Material	Federstahl
Material technisch	420-560 HV30
Oberfläche	Elektrolytisch verzinkt

Standards

NEN	2458
ISO	8752
BS	7060
DIN	1481

Info

Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to

connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	0.9
d1 (max.)	5.6
d1 (min.)	5.4
d2 ≈	3.4
D (mm)	5
L (mm)	40
s	1
V	17.54

Technische Zeichnung

