


Spiral-Spannstift, geschlitzt, schwer ISO 8752 Federstahl 420-560 HV30 Elektrolytisch verzinkt 6X60MM



Artikelnummer	39110.060.060
Marke	-
UBB	950359527872
UNSPSC	31163201
EAN	8715492807212
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Material	Federstahl
Material technisch	420-560 HV30
Oberfläche	Elektrolytisch verzinkt

Standards

ISO	8752
NEN	2458
DIN	1481
BS	7060

Info

Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction elements to each

FABORY

other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

Technische Zeichnung

