



## Spiralstifte Typ gerade DIN 7343 ISO 8750 Federstahl 420-545 HV30 1,5X8MM

Artikelnummer	39140.015.008
Marke	-
UBB	950359053226
UNSPSC	31163201
EAN	8715492807946
PKG. von 200	Nur komplette Verpackung

### Technische Parameter

Durchmesser	1.5 mm
Länge	8 mm
Material	Federstahl
Material technisch	420-545 HV30

### Standards

DIN	7343
ISO	8750

Info	Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of coiled spring-type straight pins (spiral pins): These pins are used for connections or the positioning of two or more parts and may also be used as shafts and hinge-
------	---

stop- or carrierpins, and are easily disassembled. Thanks to their spiral shaped cross section (approximately 2.1/4 coils) these pins are very flexible and suitable for repeated use with dynamic loads. Equal stress distribution throughout their cross section against the hole wall produces a good press fit, which can absorb shear forces unaffected by the direction. The pins are chamfered at both ends, so they can easily be inserted and installed automatically.

## Technische Spezifikation

a ≈	0.5
d1 (max.)	1.73
d1 (min.)	1.62
d2 (max.)	1.4
D (mm)	1.5
L (mm)	8
V	1.45

## Technische Zeichnung

