



**Spiralstifte Typ gerade DIN  
7343 ISO 8750 Federstahl  
420-545 HV30 4X28MM**

Artikelnummer	39140.040.028
Marke	-
UBB	950359057284
UNSPSC	31163201
EAN	8715492808387
PKG. von 200	Nur komplette Verpackung

**Technische Parameter**

Durchmesser	4 mm
Länge	28 mm
Material	Federstahl
Material technisch	420-545 HV30

**Standards**

ISO	8750
DIN	7343

Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.V = minimum shear strength, double, in kN.The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of coiled spring- type straight pins (spiral pins):These pins are used for connections or the positioning of two or more parts and may also be used as shafts and hinge-,
------	---

stop- or carrierpins, and are easily disassembled. Thanks to their spiral shaped cross section (approximately 2.1/4 coils) these pins are very flexible and suitable for repeated use with dynamic loads. Equal stress distribution throughout their cross section against the hole wall produces a good press fit, which can absorb shear forces unaffected by the direction. The pins are chamfered at both ends, so they can easily be inserted and installed automatically.

## Technische Spezifikation

a ≈	1.1
d1 (max.)	4.4
d1 (min.)	4.2
d2 (max.)	3.9
D (mm)	4
L (mm)	28
V	9.6

## Technische Zeichnung

