

## ISO 8748 Federstahl 420-545 HV30 3X14MM



Artikelnummer	39150.030.014
Marke	-
UBB	950359069321
UNSPSC	31163201
EAN	8715492809698
PKG. von 200	Nur komplette Verpackung

### Technische Parameter

Durchmesser	3 mm
Länge	14 mm
Material	Federstahl
Material technisch	420-545 HV30

### Standards

DIN	7344
ISO	8748

**Info**

Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of coiled spring-type straight pins (spiral pins): These pins are used for connections or the positioning of two or more parts and may also be used as shafts and hinge-, stop- or carrierpins, and are easily

disassembled. Thanks to their spiral shaped cross section (approximately 2.1/4 coils) these pins are very flexible and suitable for repeated use with dynamic loads. Equal stress distribution throughout their cross section against the hole wall produces a good press fit, which can absorb shear forces unaffected by the direction. The pins are chamfered at both ends, so they can easily be inserted and installed automatically.

### Technische Spezifikation

a ≈	0.9
d1 (max.)	3.25
d1 (min.)	3.12
d2 (max.)	2.9
D (mm)	3
L (mm)	14
V	7.6

### Technische Zeichnung

