

ISO 8748 Federstahl 420-545
HV30 5X28MM



Artikelnummer	39150.050.028
Marke	-
UBB	950359072374
UNSPSC	31163201
EAN	8715492810014
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	5 mm
Länge	28 mm
Material	Federstahl
Material technisch	420-545 HV30

Standards

DIN	7344
ISO	8748

Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.V = minimum shear strength, double, in kN.The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of coiled spring- type straight pins (spiral pins):These pins are used for connections or the positioning of two or more parts and may also be used as shafts and hinge- stop- or carrierpins, and are easily
------	---

disassembled. Thanks to their spiral shaped cross section (approximately 2.1/4 coils) these pins are very flexible and suitable for repeated use with dynamic loads. Equal stress distribution throughout their cross section against the hole wall produces a good press fit, which can absorb shear forces unaffected by the direction. The pins are chamfered at both ends, so they can easily be inserted and installed automatically.

Technische Spezifikation

a ≈	1.3
d1 (max.)	5.35
d1 (min.)	5.15
d2 (max.)	4.85
D (mm)	5
L (mm)	28
V	20

Technische Zeichnung

