

Splinte (Federstecker) DIN 94 DIN 94 Stahl Elektrolytisch verzinkt 1,6X20MM



Artikelnummer	39350.016.020
Marke	-
UBB	950359106867
UNSPSC	31163204
EAN	8715492819147
PKG. von 250	Nur komplette Verpackung

Technische Parameter

Durchmesser	1.6 mm
Länge	20 mm
Material	Stahl
Oberfläche	Elektrolytisch verzinkt

Standards

NEN	182
ISO	1234
DIN	94
NF	E25-774

Info	The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of
------	---

the nominal length
(L) is js17.

FABORY

Technische Spezifikation

a (max.)	2.5
b ≈	3.2
c (max.)	2.8
c (min.)	2.4
d (min.)	1.3
D (mm)	1.6
L (mm)	20
d (max.)	1.4

Technische Zeichnung

