



Kerbstifte in voller Länge parallel gerillt DIN 1470 DIN 1470 Automatenstahl 1,5X8MM

Artikelnummer	39700.015.008
Marke	-
UBB	950359117427
UNSPSC	31163215
EAN	8715492823038
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	1.5 mm
Länge	8 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8739
NEN	≈2601
DIN	1470

Technische Spezifikation

c ≈	0.2
d1	1.5
d2 ≈	1.6
D (mm)	1.5

Technische Zeichnung

L (mm)	8
r ≈	1.5
Tolerance	h9
V	1.6

