



Kerbstifte in voller Länge parallel gerillt DIN 1470 DIN 1470 Automatenstahl 2X16MM

Artikelnummer	39700.020.016
Marke	-
UBB	950359118417
UNSPSC	31163215
EAN	8715492823137
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	2 mm
Länge	16 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8739
DIN	1470
NEN	≈2601

Technische Spezifikation

c ≈	0.25
d1	2
d2 ≈	2.15
D (mm)	2

Technische Zeichnung

L (mm)	16
r	2
Tolerance	h9
V	2.85

FABORY

