



## Kerbstifte in voller Länge parallel gerillt DIN 1470 DIN 1470 Automatenstahl 5X24MM

|               |                          |
|---------------|--------------------------|
| Artikelnummer | 39700.050.024            |
| Marke         | -                        |
| UBB           | 950359121874             |
| UNSPSC        | 31163215                 |
| EAN           | 8715492823588            |
| PKG. von 100  | Nur komplette Verpackung |

### Technische Parameter

|             |                                                                                                                                                                                                                                                                                                                                     |
|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Durchmesser | 5 mm                                                                                                                                                                                                                                                                                                                                |
| Länge       | 24 mm                                                                                                                                                                                                                                                                                                                               |
| Material    | Automatenstahl                                                                                                                                                                                                                                                                                                                      |
| Info        | V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends. |

### Standards

|     |       |
|-----|-------|
| ISO | ≈8739 |
| DIN | 1470  |
| NEN | ≈2601 |

### Technische Spezifikation

|        |      |
|--------|------|
| c ≈    | 0.6  |
| d1     | 5    |
| d2 ≈   | 5.25 |
| D (mm) | 5    |

### Technische Zeichnung

|           |      |
|-----------|------|
| L (mm)    | 24   |
| r         | 5    |
| Tolerance | h11  |
| V         | 16.5 |

**FABORY**

