



Kerbstifte in voller Länge parallel gerillt DIN 1470 DIN 1470 Automatenstahl 8X70MM

Artikelnummer	39700.080.070
Marke	-
UBB	950359124357
UNSPSC	31163215
EAN	8715492823854
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	8 mm
Länge	70 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

NEN	≈2601
ISO	≈8739
DIN	1470

Technische Spezifikation

c ≈	1
d1	8
d2 ≈	8.3
D (mm)	8

Technische Zeichnung

L (mm)	70
r	8
Tolerance	h11
V	40.5

FABORY

