



Kerbstifte in voller Länge schräg gerillt DIN 1471 DIN 1471 Automatenstahl 1,5X20MM

Artikelnummer	39710.015.020
Marke	-
UBB	950359125180
UNSPSC	31163215
EAN	8715492823946
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	1.5 mm
Länge	20 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

DIN	1471
ISO	≈8744
NEN	≈2602

Technische Spezifikation

c ≈	0.2
d1	1.5
d2 ≈	1.6
D (mm)	1.5

Technische Zeichnung

L (mm)	20
FABORY	
$r \approx$	1.5
Tolerance	h9
V	1.6

