



Kerbstifte in voller Länge schräg gerillt DIN 1471 DIN 1471 Automatenstahl 6X50MM

Artikelnummer	39710.060.050
Marke	-
UBB	950359130453
UNSPSC	31163215
EAN	8715492824653
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	6 mm
Länge	50 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

DIN	1471
NEN	≈2602
ISO	≈8744

Technische Spezifikation

c ≈	0.8
d1	6
d2 ≈	6.3
D (mm)	6

Technische Zeichnung

L (mm)	50
FABORY	
r	6
Tolerance	h11
V	22.8

