



Kerbstifte in voller Länge schräg gerillt DIN 1471 DIN 1471 Automatenstahl 8X70MM

Artikelnummer	39710.080.070
Marke	-
UBB	950359131691
UNSPSC	31163215
EAN	8715492824813
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	8 mm
Länge	70 mm
Material	Automatenstahl

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8744
DIN	1471
NEN	≈2602

Technische Spezifikation

c ≈	1
d1	8
d2 ≈	8.35
D (mm)	8

Technische Zeichnung

L (mm)	70
r	8
Tolerance	h11
V	40.5

FABORY

