



Kerbstifte auf halber Länge schräg gerillt DIN 1472 DIN 1472 Automatenstahl 3X16MM

Artikelnummer	39720.030.016
Marke	-
UBB	950359134661
UNSPSC	31163215
EAN	8715492825179
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	3 mm
Länge	16 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

DIN	1472
ISO	≈8745
NEN	≈2603

Technische Spezifikation

c ≈	0.4
d1	3
d2 ≈	3.25
D (mm)	3

Technische Zeichnung

L (mm)	16
r	3
Tolerance	h9
V	6.15

FABORY

