



Kerbstifte auf halber Länge schräg gerillt DIN 1472 DIN 1472 Automatenstahl 8X12MM

Artikelnummer	39720.080.012
Marke	-
UBB	950359137979
UNSPSC	31163215
EAN	8715492825575
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	8 mm
Länge	12 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8745
DIN	1472
NEN	≈2603

Technische Spezifikation

c ≈	1
d1	8
d2 ≈	8.35
D (mm)	8

Technische Zeichnung

L (mm)	12
r	8
Tolerance	h11
V	40.5

FABORY

