



Kerbstifte auf halber Länge schräg gerillt DIN 1472 DIN 1472 Automatenstahl 8X70MM

Artikelnummer	39720.080.070
Marke	-
UBB	950359138969
UNSPSC	31163215
EAN	8715492825681
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	8 mm
Länge	70 mm
Material	Automatenstahl
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8745
NEN	≈2603
DIN	1472

Technische Spezifikation

c ≈	1
d1	8
d2 ≈	8.35
D (mm)	8

Technische Zeichnung

