

Flachdichtringe, Kupfer/ Festaplan, h=1.5 DIN 7603 C Kupfer/FESTAPLAN 10X14MM



Artikelnummer	50332.100.014
Marke	-
UBB	950356433454
UNSPSC	31161818
EAN	8715492244406
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	10 mm
Material	Kupfer/FESTAPLAN
Außendurchm.	14

Info

These rings are filled with asbestos-free mineral fibers (trade name "Festaplan"). Recommended operating temperature 175° C maximum. h=1.5±0.2

Standards

DIN 7604-C

Technische Spezifikation

d1	10
d1 (min.)	10.2
d2	14
d2 (max.)	13.9
D (mm)	10

Technische Zeichnung

