



KIPP Cam levers, external thread Schwarz Cast aluminium EN AC-46200/ stainless steel 1.4305 M4X12,0X10

Artikelnummer	58006.040.010
Marke	-
UBB	500689424520
UNSPSC	31162807
EAN	4059245210183
PKG. von 4	Nur komplette Verpackung

Technische Parameter

Farbe	Schwarz
D1_MM	12mm
Material	Cast aluminium/ stainless steel
Material technisch	EN AC-46200/1.4305
Gewinde	Metrisches Gewinde

Info

Material: Handles cast aluminium EN AC-46200. Thrust washer plastic PA 66 GF 35-X fibreglass reinforced. Hinge pins stainless steel 1.4305. Studs and washer steel grade 5.8. Version: Handles fine structured powder-coated, black. Thrust washer, black. Hinge pin, bright. Studs and washer zinc plated, blue passivated steel. Note: Adjustable cam

Standards

levers are used if the position of the lever relative to the axis of tension only permits one specific position (interference circle). The exact position of the lever is adjusted using a screwdriver on the fine thread setscrew. Plastics are subject to creeping under load (retardation). Drawing reference: 1) setscrew for fine adjustment of lever.adjustable

Technische Spezifikation

A	36.2
A1	41.7
B	14.4
B1	11.5
Hand force FH (N)	90
D	4
D1	12
D2	6
F	1
H	9
H1	13
L	10
S	1

Technische Zeichnung

