



KIPP Indexing plungers without collar, with locknut Metrisches feines Gewinde Stainless steel 1.4305, hardened pin 10MM

Artikelnummer	58603.000.010
Marke	-
UBB	500689881174
UNSPSC	31162807
EAN	4059245014859
PKG. von 2	Nur komplette Verpackung

Technische Parameter

D1_MM	20mm
Material	Rostfreistahl
Material technisch	1.4305
Gewinde	Metrisches feines Gewinde

Standards

Info	Material: Stainless steel threaded sleeve 1.4305 Indexing pin 1.4034 Mushroom knob black grey thermoplastic.Version: Indexing pin hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. A screw-in washer can be supplied to
------	--

help screw in the indexing plungers. The washer is slid beneath the disengaged mushroom knob so that the carrier pins engage in the slot.

Technische Spezifikation

D	10
D1	20
D2	33
F1 = springiness beginning in N	15
F2 = springiness end in N	34
F x 30°	2.8
H	10
L1	40
L2	24
L	74
P	1.5
SW	30

Technische Zeichnung

