



**KIPP Indexing plungers,
non-lockout type, with
locknut Metrisches feines
Gewinde Stainless steel
1.4305, pin not hardened,
stainless steel grip 3MM**

Artikelnummer	58685.000.003
Marke	-
UBB	500690014070
UNSPSC	31162807
EAN	4059245010707
PKG. von 2	Nur komplette Verpackung

Technische Parameter

D1_MM	6mm
Material	Rostfreistahl
Material technisch	1.4305
Gewinde	Metrisches feines Gewinde

Standards

Info	Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305. Mushroom knob 1.4305, electrolytic- polish.Version: Bright. Indexing pin not hardened, ground.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged.
------	---

Technische Spezifikation

D	3
D1	6
D2	14
F1 = springiness beginning in N	4.5
F2 = springiness end in N	10
F x 30°	0.8
H	3.5
L1	12
L2	5
L3	10
L	34.5
P	0.75
SW1	8
SW2	10

Technische Zeichnung

