



**Kugelausgleichsscheiben
DIN 6319 C 87171**

Artikelnummer	87171AMF
Marke	-
UBB	500617975312
UNSPSC	31161801
EAN	4020772087173
PKG. von 1	Nur komplette Verpackung

Technische Parameter

Info	F max = Maximum recommended static load (values do not apply to stainless steel)These spherical washers are often combined with conical seats to DIN 6319-D or DIN 6319-G. The combination enables a swing of approximately 3° in any direction to be attained, when positioning a bolt through.ATTENTION: When these washers are applied in combination with fasteners in class 10.9 or 10, the maximum allowable clamping load is at 46% of the yield strength Rp0,2 for fasteners in class 8.8 or 8 the maximum is at 66% of the yield strength Rp0,2Do not apply conical seats to DIN 6319-D with slotted holes,
------	--

Standards

DIN	6319-C
-----	--------

but use conical seats
to DIN 6319-G for
this purpose

Technische Spezifikation

Technische Zeichnung

