



Stahlwille Stecknüsse 40DL 5 MM

Artikelnummer	G0303.050.001
Marke	-
UBB	203122401284
UNSPSC	27111704
EAN	4018754000814
PKG. von 1	Nur komplette Verpackung

Technische Parameter

Applicability	Doppelsechskant
Drive size	1/4
Total length (mm)	51
Size (mm)	5

Info

Long, metric sizes:
E DIN EN 3710, E
DIN EN 3709, DIN
3124/ISO 2725-1,
ASME B 107.5M.
American sizes:
ASME B 107.1, Fed.
Spec. GGG-W-641,
SAE AS 954-E. HPQ
high performance
steel, chrome plated.

Standards

DIN	3124
-----	------