



Stiftschrauben mit 2
Sechskantmuttern UNC
ASTM A453 Superduplex
Blank Gr.660 A 7/8X135
(5.1/4)

Artikelnummer	PIMSA222135
Marke	-
UBB	500652206474
UNSPSC	00000000
EAN	
PKG. von 1	Nur komplette Verpackung

Technische Parameter

Durchmesser	7/8 Inch
Länge	135 mm
Klasse	Gr.660 A
Material	Superduplex
Oberfläche	Blank

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A453
------	------

Technische Spezifikation

L (mm)	135
--------	-----

Technische Zeichnung

FABORY

