



Kopfschraube flacher Senkkopf Schlitz UNC ASME b18.6.3 ASME B18.6.3 Messing #12-24X1/2

Artikelnummer	U48170.021.0050
Marke	-
UBB	500624967609
UNSPSC	31161504
EAN	8715492982285
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	NO.12
Länge	1/2 Inch
Antriebsart	Schlitz
Kopfform	Senkkopf
Material	Messing
Gewinderichtung	Rechts
Gewinde	Unie Gewinde grob
Threads per inch	24

Info	Screws with diameter $\leq$ No.5 and length $\leq$ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length $\leq$ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	--

Standards

ASME	B18.6.3
------	---------

Technische Spezifikation

A (max.)	0.412
H (max.)	0.132
J (max.)	0.067

Technische Zeichnung

T (max.) 0.06

FABORY

