

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M8X100

Article number	04104.080.100
Brand	-
UBB	500614315371
UNSPSC	31161620
EAN	8715494449434
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4014
DIN	931
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	100
P	1.25
s	13

Technical Drawing

