

Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 10.9 M10X110/ S=17

Article number	04104.100.110
Brand	-
UBB	500614315942
UNSPSC	31161620
EAN	8715494454469
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	110 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	110

Technical Drawing



