

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M16X110

Article number	04104.160.110
Brand	-
UBB	500614316775
UNSPSC	31161620
EAN	8715494454544
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	110 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	110
P	2

Technical Drawing



